# **Product datasheet**

Specification





# Reflex iC60H Ti24 40 A 4P curve C integrated control MCB

A9C65440

#### Main

Device Application	Control Distribution	
Range	Acti9	
Product Name	Reflex iC60	
Device Short Name	Reflex iC60H	
Product Or Component Type	Integrated control circuit breaker	
Poles Description	4P	
Number Of Protected Poles	Protected Poles 4	
Network Type	AC	
Trip Unit Technology	Thermal-magnetic	
Curve Code	С	

## Complementary

[In] Rated Current	40 A
Network Frequency	50/60 Hz
Breaking Capacity Code	Н
Breaking Capacity	30 kA lcu at 220240 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA lcu at 380415 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Ui] Rated Insulation Voltage	500 V AC
Contact Position Indicator	Yes
Control Type	Remote control by pulse ON/OFF button Remote control by continuous command Toggle
Control Signal Type	Impulse Maintained very low voltage Maintained
Local Signalling	Red LED: fault Green LED: device ON Flashing LED: device ready Flashing LED: device overheat Flashing LED: device tripped
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz 24 V AC 50/60 Hz 48 V AC 50/60 Hz 24 V DC 48 V DC
[Us] Rated Supply Voltage	230 V AC at 50/60 Hz
Mounting Mode	Fixed

Mounting Support	35 mm symmetrical DIN rail	
9 Mm Pitches	13	
Height	84 mm	
Width	117 mm	
Depth	77 mm	
Colour	White	
Mechanical Durability	50000 cycles	
Electrical Durability	AC-1: 50000 cycles AC 50 Hz	
Provision For Padlocking	Padlockable	
Locking Options Description	Padlock in OFF position	
Earth-Leakage Protection	e Protection Separate block	
Product Compatibility	With PLC	

## **Environment**

Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	3
Tropicalisation	2
Relative Humidity	93 % at 40 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	11.2 cm
Package 1 Length	16.5 cm
Package 1 Weight	880.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	14
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	12.454 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>②</b>	Halogen Free Plastic Parts Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information