Product datasheet

Specification





Acti 9 ID K - residual current circuit breaker - 4P - 40A - 30mA - type A

A9Z01440

Main

Range	Acti9
Product Name	Acti9 ID K
Product Or Component Type	Residual current circuit breaker (RCCB)
Device Short Name	ID K
Poles Description	4P
Neutral Position	Left
[In] Rated Current	40 A
Network Type	AC
Earth-Leakage Sensitivity	30 mA
Earth-Leakage Protection Time Delay	Instantaneous
Earth-Leakage Protection Class	Type A
Quality Labels	VDE

Complementary

J	
Device Location In System	Outgoer
Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	380415 V AC 50 Hz
Residual Current Tripping Technology	Voltage independent
Rated Breaking And Making Capacity	Idm 500 A Im 500 A
Rated Conditional Short-Circuit Current	GL63: Inc 4.5 kA K60: Inc 6 kA
[Ui] Rated Insulation Voltage	440 V AC 50 Hz
[Uimp] Rated Impulse Withstand Voltage	4 kV
Surge Current	250 A
Contact Position Indicator	No
Control Type	Toggle
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	8
Height	81 mm
Width	72 mm

Depth	68 mm	
Colour	White	
Mechanical Durability	5000 cycles	
Electrical Durability	AC-1: 2000 cycles	
Connections - Terminals	Biconnect top or bottom 135 mm² rigid Biconnect top or bottom 125 mm² flexible	
Wire Stripping Length	14 mm for top or bottom connection	
Tightening Torque	3.5 N.m top or bottom	

Environment

Standards	EN/IEC 61008-1 EN/IEC 61008-2-1
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	2
Electromagnetic Compatibility	8/20 μs impulse withstand, 200 A conforming to EN/IEC 61008-1
Ambient Air Temperature For Operation	-2540 °C
Ambient Air Temperature For Storage	-3070 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.600 cm
Package 1 Width	8.500 cm
Package 1 Length	9.000 cm
Package 1 Weight	346.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	27
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.829 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	216
Package 3 Height	80.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	90.632 kg

Contractual warranty

Warranty 12 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations