Product datasheet

Specifications





Acti 9 ID K - residual current circuit breaker - 4P - 40A - 300mA - type A

A9Z04440

Main

Range	Acti9
Product Name	Acti9 ID K
Product Or Component Type	Residual current circuit breaker (RCCB)
Device Short Name	ID K
Poles Description	4P
Neutral Position	Left
[In] Rated Current	40 A
Network Type	AC
Earth-Leakage Sensitivity	300 mA
Earth-Leakage Protection Time Delay	Instantaneous
Earth-Leakage Protection Class	Туре А
Quality Labels	VDE

Complementary

Device Location In System	Outgoer
Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	380415 V AC 50 Hz
Residual Current Tripping Technology	Voltage independent
Rated Breaking And Making Capacity	Idm 500 A Im 500 A
Rated Conditional Short-Circuit Current	GL63: Inc 4.5 kA K60: Inc 6 kA
[Ui] Rated Insulation Voltage	440 V AC 50 Hz
[Uimp] Rated Impulse Withstand Voltage	4 KV
Surge Current	250 A
Contact Position Indicator	No
Control Type	Toggle
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	8
Height	81 mm
Width	72 mm

Depth	68 mm
Colour	White
Mechanical Durability	5000 cycles
Electrical Durability	AC-1: 2000 cycles
Connections - Terminals	Biconnect top or bottom 135 mm² rigid Biconnect top or bottom 125 mm² flexible
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	3.5 N.m top or bottom

Environment

EN/IEC 61008-1 EN/IEC 61008-2-1
IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
2
8/20 μs impulse withstand, 200 A conforming to EN/IEC 61008-1
-2540 °C
-3070 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.800 cm
Package 1 Width	7.500 cm
Package 1 Length	9.000 cm
Package 1 Weight	340.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	27
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.684 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations