Product datasheet

Specifications





VarPlus Can HDuty Capacitor -15/18 kvar - 440 V - 50/60Hz

BLRCH150A180B44

Main

Range Of Product	PowerLogic	
Product Or Component Type	Heavy duty capacitor	
Network Frequency	50/60 Hz	
Series Name	HDuty	
Network Harmonic Content	<= 20 %	
Electrical Parameters	15 kvar 440 V 50 Hz 18 kvar 440 V 60 Hz	
Maximum Permissible Voltage	1.1 x Un (8 hours over 24 hours)	
Continuous Overcurrent Capacity	current Capacity 1.8 x In	
Rated Voltage	440 V AC 50/60 Hz	

Complementary

Complementary		
Dielectric Losses	< 0.2 W/kvar	
Power Losses	< 0.5 W/kVAr	
Capacitance Tolerance	- 5 % to 10 %	
Voltage Test	2.15 x Un AC between terminals for 10 s <= 660 V - 3 kV AC between terminal and container for 10 s >= 660 V - 6 kV AC between terminal and container for 10 s	
Inrush Current	250 x ln	
Maximum Switching Operation Per Year	Operation 7000	
Service Life In Hours	130000 h	
Dielectric Material	Metallized polypropylene film with Zn/Al alloy, special resistivity & profile, special edge (wave cut)	
Impregnation Material	Non-PCB dry PUR resin Biodegradable	
Type Of Installation	Indoor installation	
Connections - Terminals	ClampTite terminal	
Mounting Mode	Upright/horizontal	
Diameter	r 90 mm	
Height	242 mm	
Net Weight	1.6 kg	

Environment

Standards	IEC 60831-2 IEC 60831-1
Ip Degree Of Protection	IP20
Operating Altitude	2000 m
Temperature Class	D
Ambient Air Temperature For Operation	-2555 °C
Relative Humidity	95 %

Packing Units

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	28.5 cm
Package 1 Width	11 cm
Package 1 Length	11.8 cm
Package 1 Weight	1.7 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	2
Package 2 Height	29 cm
Package 2 Width	29 cm
Package 2 Length	39 cm
Package 2 Weight	7.5 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	6
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	12.6 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins