





Easy Rack 600mm/24U/800mm, with Roof, Side panel, castors, feet and 4 Brackets, No Bottom, black

ER6482

Overview

Lead Time Usually in Stock

Main

Product Or Component Type	Rack enclosure
Number Of Rack Unit	24U
Provided Equipment	Baying hardware Key(s)
	Keyed-alike doors and side panels
	Leveling feet
	Mounting hardware
	Pre-installed casters
	Side panels

Physical

Height	119.8 cm
Width	60 cm
Depth	80 cm
Net Weight	68.4 kg
Colour	Black
Maximum Mounting Depth	64.14 cm
Minimum Mounting Depth	19.05 cm
Rack Width	19"
Marking	18 gauge front door 19 gauge rear door 16 gauge post 14 gauge EIA mounting rail
Permanent Permissible Load	1199.75 kg static 599.65 kg

Conformance

Standards UL 2416 UL 60950-1 EIA-310E

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	133 cm

Package 1 Width	65 cm	
Package 1 Length	85 cm	
Package 1 Weight	74 ka	

Contractual warranty

Warranty 5 year repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile