

# Product datasheet

Specifications



## Easy Rack 800mm/42U/1200mm with Roof, Side panel, castors, feet and 4 Brackets, No Bottom, black

ER8222

### Overview

Lead time Usually in Stock

### Main

Number of rack unit 42U

Provided equipment Baying hardware  
Key(s)  
Keyed-alike doors and side panels  
Leveling feet  
Mounting hardware  
Pre-installed casters  
Side panels

### Physical

Colour Black

Height 199.1 cm

Width 80 cm

Depth 120 cm

Net weight 135 kg

Mounting mode Not rack-mountable

Maximum mounting depth 104.14 cm

Minimum mounting depth 24.16 cm

Rack width 19"

Marking 18 gauge front door  
19 gauge rear door  
16 gauge post  
14 gauge EIA mounting rail

Permanent permissible load 1199.75 kg static  
599.65 kg dynamic

### Conformance

Standards UL 2416  
EIA-310E

### Packing Units

Number of Units in Package 1 1

Package 1 Weight 144 kg

|                  |        |
|------------------|--------|
| Package 1 Height | 212 cm |
| Package 1 width  | 125 cm |
| Package 1 Length | 85 cm  |
| Pallet layers    | 1      |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>                     |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |

## Contractual warranty

|          |                          |
|----------|--------------------------|
| Warranty | 5 year repair or replace |
|----------|--------------------------|