





Easy Rack 800mm/42U/800mm with Roof, Side panel, castors, feet and 4 Brackets, No Bottom, black

ER8282

Overview

Lead Time Usually in Stock

Main

Product Or Component Type	Rack enclosure
Number Of Rack Unit	42U
Provided Equipment	Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels

Physical

•	
Height	199.1 cm
Width	80 cm
Depth	80 cm
Net Weight	120.8 kg
Colour	Black
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	64.14 cm
Minimum Mounting Depth	19.05 cm
Rack Width	19"
Marking	18 gauge front door
	19 gauge rear door
	16 gauge post
	14 gauge EIA mounting rail
Permanent Permissible Load	1199.75 kg static
	599.65 kg dynamic

Conformance

 Standards
 UL 60950-1

 UL 2416
 EIA-310E

Packing Units

Unit Type Of Package 1 PCE

Number Of Units In Package 1	1
Package 1 Height	212 cm
Package 1 Width	85 cm
Package 1 Length	85 cm
Package 1 Weight	128 ka

Contractual warranty

Warranty 5 year repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile