Product datasheet

Specification





EVlink Wallbox - 22 kW - T2 socket outlet - charging station

EVH2S22P02K

Main

Range	EVlink
Product Name	EVlink Wallbox
Product Or Component Type	Charging station
Device Short Name	EVH2
Poles Description	3P + N
Mounting Mode	Wall-mounted
Offer Type	Standard
Max Power	22 kW 32 A
Number Of Charge Point	1
Connection To The Vehicle	Socket-outlet T2
Access Control System	Key

Complementary

Rated Supply Voltage	380415 V AC 50/60 Hz
Earthing System	π
	TN
Number Of Inputs	1
Input Type	Contact for power limitation
	Contact for delayed charging
Control Type	1 white button, function: stop/restart
	Green button, function: cable unlocking
Local Signalling	1 multi-colour LED, function: status indication
Height	480 mm
Width	331.5 mm
Depth	170 mm
Net Weight	5.6 kg
Colour	White (RAL 9003)
	Grey (RAL 7016)
Standards	IEC 62196-2
	IEC 62196-1
	IEC 61851-22
	IEC 61851-1
Product Certifications	СВ
	CE

Environment

Ip Degree Of Protection	IP54 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ambient Air Temperature For Operation	-3050 °C
Ambient Air Temperature For Storage	-4080 °C
Relative Humidity	595 %

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	27.000 cm
Package 1 Width	40.000 cm
Package 1 Length	53.500 cm
Package 1 Weight	8.349 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	4
Package 2 Height	75.000 cm
Package 2 Width	80.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	41.396 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information