Product datasheet

Specification





gearbox straight teeth GBX - Ø 60 mm - reduction 40:1 < 12 arc.min - 40 N.m

GBX060040K

Main

Range Compatibility	Lexium 62 ILM						
3	Lexium ILE						
	Lexium ILA						
	Lexium 52						
	Lexium 62						
	Lexium 32						
	Lexium ILS						
Product Or Component Type	Planetary gearbox						
Gear Box Type	Straight teeth						
Device Short Name	GBX						
Product Compatibility	BSH (55 mm, 1 motor stacks)						
	ILE (66 mm, 1 motor stacks)						
	ILE (66 mm, 2 motor stacks)						
	ILA (57 mm, 1 motor stacks)						
	ILA (57 mm, 2 motor stacks)						
	ILS (57 mm, 1 motor stacks)						
	ILS (57 mm, 2 motor stacks)						
	ILS (57 mm, 3 motor stacks)						
	SH3						
	MH3						
	ILM						
Gearbox External Diameter	60 mm						
Reduction Ratio	40:1						

Complementary

Maximum Torsional Backlash	12 arc.min
Torsional Rigidity	2.5 N.m/arcmin
Housing Colour	Black
Housing Material	Black anodized aluminium
Shaft Material	C 45
Additional Information	Lubricated for life
Service Life In Hours	30000 h at 100 rpm at 30 °C
Mounting Position	Any position
Efficiency	94 %
Maximum Radial Force Fr	340 N at 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 $^{\circ}\text{C}$
Maximum Axial Force Fa	450 N at 100 rpm, during 30000 hour at 30°C
Moment Of Inertia	0.064 kg.cm²
Continuous Output Torque	40 N.m at 100 rpm at 30 °C
Maximum Output Torque	64 N.m at 100 rpm at 30 °C

Net Weight	1.1 kg	
Input Diameter	14.0 mm	

Environment

Noise Level	58 dB at 1 m, no-load			
Ip Degree Of Protection	Shaft output: IP54			
Ambient Temperature For Operation	-2590 °C			

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.600 cm
Package 1 Width	9.400 cm
Package 1 Length	17.200 cm
Package 1 Weight	1.030 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	10.801 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >


Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance




Certifications & Standards

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	No need of specific recycling operations				

GBX060040K

Dimensions Drawings

Dimensions with Servo Motor Adaptation Kit



- (1) GBK adaptation kit
- (2) GBK adaptation kit related dimensions a1, c, Ø6, Ø7, Ø8 depend on the gearbox and servo motor combination
- Ø8 shaft end adaptor in case motor shaft diameter is smaller than gearbox input coupling diameter

Values in mm

a2	а3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
67.5	35	30	2.5	16	5	60	40 h7	14 h7	M5 x 8	52

Values in in

values in in.										
a2	a3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
2.66	1.38	1.18	0.10	063	0.19	2.36	1.57 h7	0.55 h7	M5 x 0.31	2.05