Product datasheet

Specifications

Sreen Premium™



Unica Top/Class - rocker switch -1-way - 10 AX 250 VAC - 2 m graph.

MGU3.201.12N

() Discontinued on: 30 Sept 2023

① Discontinued

Main

Range Of Product	Unica
Aesthetic Name	Unica Top - Unica Class
Product Or Component Type	Switch
Device Presentation	Mechanism
Technology Type	Electromechanical
Switch Function	1-pole 1-way
Number Of Rocker	1
Device Application	Light control
Provided Equipment	Internal power connection
Colour Tint	Graphite

Complementary

Rated Current	10 AX
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Electrical Durability	10000 cycles
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening Distance	> 3 mm
Actuator	Rocker
Number Of Modules	2 modules
Pilot Light	LED, colour: blue, current consumption: 0.15 mA, temperature rise: 15 °C
Connections - Terminals	Screwless terminals
Cable Cross Section	02.5 mm² rigid cable 02.5 mm² flexible cable
Material	ABS (acrylonitrile butadiene-styrene): mechanism cover
Fixing Mode	Clip-in
Width	45 mm
Height	45 mm

Depth	34 mm
Embedding Depth	22 mm
Net Weight	0.023 kg
Ambient Air Temperature For Operation	2535 °C
Ambient Air Temperature For Storage	050 °C
Standards	EMC directive EN 60669-1 LV directive
Product Certifications	14.10.01/5433

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Environmental Characteristic	Petrol
	Bleach
	Alcohol
	UV resistant
	Acetone
	Window-cleaning fluid
	Oil
	Liquid soap

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	6.500 cm
Package 1 Length	6.500 cm
Package 1 Weight	26.500 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	4.500 cm
Package 2 Width	13.500 cm
Package 2 Length	33.000 cm
Package 2 Weight	330.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	4.195 kg

Contractual warranty

Warranty

12 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations