

# Product datasheet

Specifications



## SpaceLogic KNX Universal Dimmer Master 2 channel

MTN6710-0102

### Main

Range Of Product	SpaceLogic KNX
Product Or Component Type	Dimming actuator
Operating Mode	KNX bus system
Bus Type	KNX

### Complementary

Mounting Support	DIN rail
[Ue] Rated Operational Voltage	230 V
Network Frequency	50/60 Hz
Number Of Outputs	2
Load Type	LV halogen: 20...350 W at 230 V Incandescent lamp: 20...350 W at 230 V Halogen lamp: 20...350 W at 230 V RC LED lamp: 2...200 W at 230 V RL LED lamp: 2...60 W at 230 V

### Environment

Ip Degree Of Protection	IP20
-------------------------	------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.400 cm
Package 1 Width	12.800 cm
Package 1 Length	15.900 cm
Package 1 Weight	269.000 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	28
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	8.350 kg

### Contractual warranty

---

Warranty

18 months

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Mercury Free

Rohs Exemption Information [Yes](#)

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)