# **Product datasheet**

Specification





# Spacial CRNG tspt door w/o mount.plate. H1000xW800xD400 IP66 IK08 RAL7035

NSYCRNG108400T

! Discontinued on: 31 May 2023

! End-of-service on: 30 Sept 2023

#### ① To be discontinued

#### Main

Range	Spacial
Product Name	Spacial CRNG
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	1000 mm
Enclosure Nominal Width	800 mm
Enclosure Nominal Depth	400 mm
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 door 1 lock 2 cable gland plate: bottom
Door Type	Glazed
Mounting Plate Description	Without mounting plate

## Complementary

Body Type	Single piece body
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 5 mm double-bar
Type Of Gland Plate	Standard
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	Body: steel Door: steel and security glass
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	UL cUL
Net Weight	45 kg

## **Environment**

Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

# **Packing Units**

r adming dimes	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	44.5 cm
Package 1 Width	82.5 cm
Package 1 Length	102.0 cm
Package 1 Weight	40.75 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	4
Package 2 Height	178.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	178.0 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations