# **Product datasheet**

Specification





### wall-mounting enclosure polyester monobloc IP66 H1056xW852xD350mm glazed door

NSYPLM108TG

#### Main

Range	Thalassa	
Product Name	Thalassa PLM	
Device Short Name	PLM	
Enclosure Type	Multi-purpose	
Category	Compact enclosure	
Nominal Height	1056 mm	
Nominal Width	852 mm	
Nominal Depth	350 mm	
Enclosure Mounting	Wall mounted	
Device Composition	1 body 1 door 1 lock	
Door Type	Transparent	
Lock Type	4 points lock, handle with 5 mm double bar insert	

### Complementary

Number Of Locks	1
Mounting Plate Description	Without mounting plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
	Body: polyester reinforced with fibreglass Door: tempered glass
Colour	Grey (RAL 7035)
Standards	IEC 62208 NEMA classification 4X NEMA classification 13
Product Certifications	UL
Electrical Insulation Class	Class II

#### **Environment**

Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For	-4080 °C

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	88 cm
Package 1 Width	38 cm
Package 1 Length	109 cm
Package 1 Weight	35.494 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	4
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	165 cm
Package 2 Weight	145 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations