Product datasheet





Spacial SF enclosure without mounting plate - assembled -1800x600x600 mm

NSYSF18660

Main

Range	Spacial
Extended Range	Spacial SF
Application	Multi-purpose
Product Or Component Type	Suitable enclosure
Enclosure Nominal Height	1800 mm
Enclosure Nominal Width	600 mm
Enclosure Nominal Depth	600 mm
Enclosure Mounting	Floor-standing
Device Composition	2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle: door 1 rear panel 1 roof

Complementary

Structure Type	Perforated structure with a pitch of 25 mm
	Panels and doors built into the structure
	Vertical uprights joined with top and bottom frames
	Formed from a single section
Door Opening Side	Reversible (120 °)
Door Type	Plain front
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Lock Type	4 points lock, handle with 5 mm double bar insert front door
Number Of Doors	Front: 1 door(s)
Accessibility For Operation	Front
	Rear
	Sides of enclosure
Removable Parts	Door by screws hinge
	Rear panel by screws
	Roof by screws
	Mounting plate bracket by screws
	Sliding rail by screws
	Sliding fall by screws
Material	Frame: galvanised steel
	Uprights: galvanised steel
	Door: sheet steel
	Panels: sheet steel
	Hinge: zamak
	· · · · · · · · · · · · · · · · · · ·
	Handle: polyamide 6 with 30 % fibre glass

Life Is On Schneider 25 Apr 2024

Surface Finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)
Net Weight	106 kg

Environment

Standards	IEC 62208
Nema Degree Of Protection	NEMA 3R/12
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	64.5 cm
Package 1 Width	69.0 cm
Package 1 Length	193.0 cm
Package 1 Weight	83.0 kg

Contractual warranty

Warranty 12 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations