# **Product datasheet**

Specifications





### ABS box IP66 IK07 RAL7035 Int.H125W80D65 Ext.H138W93D72 Transp.cover H20

NSYTBS1397T

### Main

Range	Thalassa	
Product Name	Thalassa TBS	
Device Application	Multi-purpose	
Category	y Industrial box	
Height	138 mm	
Width	93 mm	
Depth	h 72 mm	
Internal Height	nal Height 125 mm	
Internal Width 80 mm		
Internal Depth	65 mm	
Enclosure Mounting	Wall mounted	
Device Composition	1 body 1 cover 4 cover screw	
Quantity Per Set	Set of 2	
Body Type	One piece moulded	
Type Of Front Cover	Low transparent cover	
Cover Fixing	ing Plastic screws	
Lock Type	Captive screw flat outside sealed area	
Removable Parts	Cover by captive screws	

### Complementary

,		
Material	ABS (acrylonitrile butadiene-styrene)	
Colour	Grey (RAL 7035) Transparent	
Standards	IEC 62208	
Product Certifications	TÜV	
Electrical Insulation Class	Class II	
Ip Degree Of Protection	IP66 conforming to NEMA 4.4X	
Ik Degree Of Protection	IK07 conforming to IEC 62262	
Glow Wire Resistance	650 °C conforming to IEC 60695-2-11	
Ambient Air Temperature For Storage	-1540 °C	

Operating Temperature	-2560 °C
Net Weight	0.23 kg

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	14.5 cm
Package 1 Length	20 cm
Package 1 Weight	230 g
Unit Type Of Package 2	PAM
Number Of Units In Package 2	1450
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	215 cm
Package 2 Weight	379 kg

## **Contractual warranty**

Warranty 12 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations