

Product datasheet

Specifications



braking resistor - IP 20 - 25 Ohm - 9.8 kW

VW3A7803

⚠ Discontinued on: 23 Jul 2021

⚠ To be discontinued

Main

Range Of Product	Altivar
Range Compatibility	Altivar 71
Product Compatibility	ATV71HD11Y ATV71HU22M3 ATV71HU75N4 ATV71HU75Y ATV71PU75N4Z ATV71WU75N4 ATV71HD11N4 ATV71HU30M3 ATV71HU40M3 ATV71PD11N4Z ATV71WD11N4
Ohmic Value	24.5 Ohm

Complementary

Average Power Available	9.8 kW at 50 °C
Electrical Connection	M10 bar wire
Protection Type	Thermal protection via thermal overload relay
Width	610 mm
Height	440 mm
Depth	540 mm
Net Weight	28 kg

Environment

Ip Degree Of Protection	IP23
Ambient Air Temperature For Storage	-25...75 °C
Ambient Air Temperature For Operation	0...50 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	12 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration