

Product datasheet

Specifications



Metal conduit box UL Nema type1 - IP21 - for variable speed drive - size 6

VW3A9704

Main

Range Of Product	Altivar
Accessory / Separate Part Category	Protection accessory
Accessory / Separate Part Type	IP21 protection kit
Product Compatibility	Variable speed drive ATV630 motor at 55 kW, normal duty 200...240 V Variable speed drive ATV630 motor at 75 kW, normal duty 200...240 V Variable speed drive ATV630 motor at 110 kW, normal duty 380...480 V Variable speed drive ATV630 motor at 132 kW, normal duty 380...480 V Variable speed drive ATV630 motor at 160 kW, normal duty 380...480 V Variable speed drive ATV630 motor at 90 kW, heavy duty 380...480 V Variable speed drive ATV630 motor at 110 kW, heavy duty 380...480 V Variable speed drive ATV630 motor at 132 kW, heavy duty 380...480 V Variable speed drive ATV610 motor at 110 kW 380...480 V Variable speed drive ATV610 motor at 132 kW 380...480 V Variable speed drive ATV610 motor at 160 kW 380...480 V Variable speed drive ATV930 motor at 55 kW, normal duty 200...240 V Variable speed drive ATV930 motor at 75 kW, normal duty 200...240 V Variable speed drive ATV930 motor at 110 kW, normal duty 380...480 V Variable speed drive ATV930 motor at 132 kW, normal duty 380...480 V Variable speed drive ATV930 motor at 160 kW, normal duty 380...480 V Variable speed drive ATV930 motor at 45 kW, heavy duty 200...240 V Variable speed drive ATV930 motor at 55 kW, heavy duty 200...240 V Variable speed drive ATV930 motor at 90 kW, heavy duty 380...480 V Variable speed drive ATV930 motor at 110 kW, heavy duty 380...480 V Variable speed drive ATV930 motor at 132 kW, heavy duty 380...480 V
Accessory / Separate Part Destination	Variable speed drive
Range Compatibility	Easy Altivar 610 Altivar Process ATV600 Altivar Process ATV900

Complementary

Kit Composition	Instruction sheet Fixing accessories All the mechanical parts including a pre-cut plate for fixing the cable glands
Net Weight	9 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	31.500 cm
Package 1 Width	37.100 cm
Package 1 Length	40.500 cm
Package 1 Weight	10.463 kg
Unit Type Of Package 2	P12

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	18
Package 2 Height	110.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	201.500 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
✓ Pvc Free	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration