

Product datasheet

Specifications



booted head for pushbutton XAC-B -
black - 16 mm, -25..+70 °C

XACB9212

Main

Range of product	Harmony XAC
Product or component type	Head for push-button
Component name	XACB
Marking	Unmarked
Operator additional information	Booted
Operating travel	16 mm
Cap/Operator or lens colour	Black
Product compatibility	XESD1281 XESD1191 XESD1181 XESD1291
Sale per indivisible quantity	10

Complementary

Net weight	0.005 kg
------------	----------

Environment

Standards	EN 60947-5-1 CSA C22.2 No 14 IEC 60947-5-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	100 gn conforming to IEC 60068-2-27
Electrical shock protection class	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 50102

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Weight	6 g
Package 1 Height	3 cm
Package 1 width	14 cm
Package 1 Length	18 cm
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Weight	69 g
Package 2 Height	18 cm
Package 2 width	3 cm
Package 2 Length	14 cm
Unit Type of Package 3	S02
Number of Units in Package 3	200
Package 3 Weight	1.706 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration

Contractual warranty

Warranty	12 months
----------	-----------