

# Product datasheet

Specifications



core balance current transformer  
CSH200 - Sepam series  
20,40,60,80 - diam. 200mm

59636

## Main

Range Of Product	Sepam series 48 Sepam series 80 NPP Sepam series 60 Sepam series 20 Sepam series 80 Sepam series 40
------------------	--

Device Short Name	CSH200
-------------------	--------

## Complementary

Current Transformer Type	Core balance
Current Transformer Ratio	1/470
Permissible Current	20 kA during 1 s
Mounting Support	Cables Mounting plate
Width	274 mm
Height	256 mm
Depth	46 mm
Diameter	196 mm inner:
Net Weight	1.4 kg

## Environment

Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	26.9 cm
Package 1 Length	28.1 cm
Package 1 Weight	1.64 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	5
Package 2 Height	30 cm
Package 2 Width	30 cm

<b>Package 2 Length</b>	40 cm
<b>Package 2 Weight</b>	8.52 kg
<b>Unit Type Of Package 3</b>	P12
<b>Number Of Units In Package 3</b>	40
<b>Package 3 Height</b>	50 cm
<b>Package 3 Width</b>	80 cm
<b>Package 3 Length</b>	120 cm
<b>Package 3 Weight</b>	81.176 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

---

✓ Toxic Heavy Metal Free

---

✓ Mercury Free

---

✓ Rohs Exemption Information Yes

---

## Certifications & Standards

**Reach Regulation**

[REACH Declaration](#)

---

**Eu Rohs Directive**

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

---

**China Rohs Regulation**

[China RoHS declaration](#)

---

**Circularity Profile**

No need of specific recycling operations

---