

Product datasheet

Specifications



PowerLogic BVE Red/Green LED standard outdoor Light indicator

59988

Main

Range Compatibility	Easergy T300 Easergy Flair
Product Or Component Type	Indicator lamp
Device Short Name	BVE
Fixing Mode	By 2 screws, with diameter 4 mm
[Us] Rated Supply Voltage	3.6 V, <40 mA
Mounting Mode	Wall mount

Complementary

Connections - Terminals	Screw terminals 3, cable cross section: 1.5 mm²
Local Signalling	LED
Luminous Flux	6 lm
Width	70 mm
Height	121 mm
Depth	150 mm
Net Weight	0.147 kg

Environment

Ip Degree Of Protection	IP54
Ik Degree Of Protection	IK09

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	8.7 cm
Package 1 Length	13.0 cm
Package 1 Weight	150.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	64
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	60.0 cm
Package 2 Weight	10.2 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration