Product datasheet





PratiKa wander socket - straight -63 A - 3P + N + E - 200...250 V AC - IP67

81480

! Discontinued on: 03-Jul-2023

! Discontinued

Main

Range	PratiKa
Product Or Component Type	Wander socket
Device Short Name	PratiKa socket
Plug, Socket Category	Low voltage
Poles Description	3P + N + E
Network Type	AC
Outlet Standard	Industrial

Complementary

Plug, Socket, Control Station Shape	Straight
[In] Rated Current	63 A
[Ue] Rated Operational Voltage	200250 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	9 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Pins: stainless steel Sleeves: nickel plated brass Springs: stainless steel
Connections - Terminals	Captive screws
Cable Cross Section	625 mm²
Cable Outer Diameter	1731 mm
Cable Entry	Cable gland
Thread Type	Pg 36
Net Weight	0.787 kg
Height	110 mm
Width	110 mm
Depth	265 mm
Colour	Grey (RAL 7035)
Voltage Colour	Blue

Environment

Standards	IEC 60309-2
	IEC 60309-1
Ip Degree Of Protection	IP67 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 62262
Fire Resistance	850 °C conforming to IEC 60695-2-1
Relative Humidity	50 % at 40 °C
	70 % at 30 °C
	90 % at 20 °C
Ambient Air Temperature For Operation	35 °C (86400 s)
	-2540 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	11.0 cm
Package 1 Length	26.5 cm
Package 1 Weight	780.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	8.287 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Circularity Profile	No need of specific recycling operations
	Product out of China RoHS scope. Substance declaration for your information
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Compliant with Exemptions
Reach Regulation	REACh Declaration