

Product datasheet

Specifications



miniature circuit breaker - xC60 - 3 poles - 10 A - C curve

A9N3P10C

Main

Device application	Distribution
Range of product	Acti9
Range	Acti9
Product name	XC60
Product or component type	Miniature circuit-breaker
Device short name	xC60
Poles description	3P
Number of protected poles	3
[In] rated current	10 A
Network type	AC DC
Trip unit technology	Thermal-magnetic
Curve code	C
Utilisation category	Category A conforming to EN/IEC 60947-2
Suitability for isolation	Yes conforming to EN/IEC 60947-2

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	240 V AC 50/60 Hz 380...415 V AC 50/60 Hz 100...125 V DC
Magnetic tripping limit	8 x In +/- 20 %
Breaking capacity	10000 A Icn at 240 V AC 50/60 Hz conforming to EN/IEC 60898-1 10000 A Icn at 415 V AC 50/60 Hz conforming to EN/IEC 60898-1 15 kA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA Icu at 100...125 V DC conforming to EN/IEC 60947-2
[Ics] rated service breaking capacity	7.5 kA conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 15 kA conforming to EN/IEC 60947-2 - 100...125 V DC
Limitation class	3 conforming to EN/IEC 60898-1 3 conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Contact position indicator	Yes

Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	35 mm DIN rail
Comb busbar and distribution block compatibility	Top: YES
9 mm pitches	6
Height	85 mm
Width	54 mm
Depth	77.5 mm
Net weight	0.31 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	20000 cycles
Connections - terminals	Tunnel type terminals (bottom) 16 mm ² flexible Tunnel type terminals (bottom) 25 mm ² rigid Biconnect (top)
Wire stripping length	13 mm for top or bottom connection
Tightening torque	2 N.m
Earth-leakage protection	Separate block
Product compatibility	C60 auxiliary C60 accessories

Environment

Standards	EN/IEC 60947-2 EN/IEC 60898-1
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-30...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	5.0 cm
Package 1 Length	8.0 cm
Package 1 Weight	328.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free plastic parts & cables product

Recommended replacement(s)