# **Product datasheet**

Specifications





# Acti 9 Isolator xSW 4P 63A 2.5kA 415V AC

A9S4P063

#### Main

Range Of Product	ISW 40125
Range	Acti9
Product Or Component Type	Isolator
Device Application	Isolation

## Complementary

• •	
[Ie] Rated Operational Current	63 A at 415 V AC
[Ui] Rated Insulation Voltage	6 kV
[Uimp] Rated Impulse Withstand Voltage	500 V
Poles Description	4P
Rated Breaking Capacity	2.5 kA
Short-Circuit Withstand	20 A
[Us] Rated Supply Voltage	48 V DC 1P 100 V DC 2P
Utilisation Category	AC-22
Total Number Of 18 Mm Modules	4
Product Destination	Distribution board

### Environment

Ambient Air Temperature For Operation	-2050 °C
Pollution Degree	3
Standards	IEC 60669-1 IEC 60947-3

### **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	7.6 cm
Package 1 Length	8.4 cm
Package 1 Weight	339 g

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

<b>S</b>	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	