# **Product datasheet**

Specifications



# Actassi - cable - category 6 - 4 pair - FTP - 305m - blue - CM



ACT4P6SCM3RBBU



#### Main

Range	Actassi
Product Or Component Type	Copper cable
Colour Tint	Blue
Cable Shielding Type	F/UTP

### Complementary

Type Of Cable	4 pair cables
Communication Network Category	6
Minimum Return Loss	Guaranteed: 19.4 dB at 0.772 MHz
	Guaranteed: 20 dB at 1 MHz
	Guaranteed: 23 dB at 4 MHz
	Guaranteed: 24.5 dB at 8 MHz
	Guaranteed: 25 dB at 10 MHz
	Guaranteed: 25 dB at 16 MHz
	Guaranteed: 25 dB at 20 MHz
	Guaranteed: 24.3 dB at 25 MHz
	Guaranteed: 23.6 dB at 31.25 MHz
	Guaranteed: 21.5 dB at 62.5 MHz
	Guaranteed: 20.1 dB at 100 MHz
Attenuation	Guaranteed: 1.8 dB @ 0.772 MHz per 100 m cable
	Guaranteed: 2 dB @ 1 MHz per 100 m cable
	Guaranteed: 4.1 dB @ 4 MHz per 100 m cable
	Guaranteed: 5.8 dB @ 8 MHz per 100 m cable
	Guaranteed: 6.5 dB @ 10 MHz per 100 m cable
	Guaranteed: 8.2 dB @ 16 MHz per 100 m cable
	Guaranteed: 9.3 dB @ 20 MHz per 100 m cable
	Guaranteed: 10.4 dB @ 25 MHz per 100 m cable
	Guaranteed: 11.7 dB @ 31.25 MHz per 100 m cable
	Guaranteed: 17 dB @ 62.5 MHz per 100 m cable
	Guaranteed: 22 dB @ 100 MHz per 100 m cable
Power Sum Near-End Crosstalk	Guaranteed: 64 dB at 0.772 MHz
[Psnext]	Guaranteed: 62.3 dB at 1 MHz
	Guaranteed: 53.3 dB at 4 MHz
	Guaranteed: 48.8 dB at 8 MHz
	Guaranteed: 47.3 dB at 10 MHz
	Guaranteed: 44.3 dB at 16 MHz
	Guaranteed: 42.8 dB at 20 MHz
	Guaranteed: 41.3 dB at 25 MHz
	Guaranteed: 39.9 dB at 31.25 MHz
	Guaranteed: 35.4 dB at 62.5 MHz
	Guaranteed: 32.3 dB at 100 MHz

Guaranteed: 67 dB at 0.772 MHz
Guaranteed: 65.3 dB at 1 MHz
Guaranteed: 56.3 dB at 4 MHz
Guaranteed: 51.8 dB at 8 MHz
Guaranteed: 50.3 dB at 10 MHz
Guaranteed: 47.3 dB at 16 MHz
Guaranteed: 45.8 dB at 20 MHz
Guaranteed: 44.3 dB at 25 MHz
Guaranteed: 42.9 dB at 31.25 MHz
Guaranteed: 38.4 dB at 62.5 MHz
Guaranteed: 35.3 dB at 100 MHz
100 Ohm (+/- 6) at 1100 MHz
73.2 Ohm
330 pF / 100 m
5 %
PE
Solid bare copper
AWG 24
4.9 mm
305 m

### Environment

Ambient Air Temperature For Operation	75 °C
Product Certifications	UL
Flame Retardance	СМ
Standards	ANSI/TIA/EIA-568-B ISO/IEC 11801 UL 444

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	16 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations