Product datasheet

Specifications





Clipsal X switch 1-way 16A white

CPX161SW1M_WE

Main

Range	Clipsal
Product Or Component Type	Switch
Device Application	Control
Colour Tint	White
Type Of Packing	Group
Colour Tint	White

Complementary

· · · · · · · · · · · · · · · · · ·	
Device Presentation	Mechanism
Technology Type	Electromechanical
Number Of Rocker	1
Device Mounting	Flush
Switch Function	1-way
Control Type	Rocker
Rated Current	16 A at 240 V AC 50 Hz
Number Of Modules	1
Material	PC: front cover PA6: back cover
Connections - Terminals	Shrouded terminals
Width	21 mm
Height	48 mm
Depth	37 mm
Resistance To Chemical Agents	Not resistant to alcohols Not resistant to cleaning agent Not resistant to thinner

Environment

Ambient Air Temperature For Operation	-535 ℃
Ambient Air Temperature For Storage	-535 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use
Product Certifications	ISI
Standards	IS 3854

Ip Degree	Of	Protection
-----------	----	------------

IP20

Packing Units

r dening ennie	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.54 cm
Package 1 Width	4.44 cm
Package 1 Length	6.35 cm
Package 1 Weight	15 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	20
Package 2 Height	5.5 cm
Package 2 Width	10 cm
Package 2 Length	23.5 cm
Package 2 Weight	401 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	240
Package 3 Height	24.5 cm
Package 3 Width	26 cm
Package 3 Length	33 cm
Package 3 Weight	4.21 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	