Product datasheet

Specification





Clipsal X switch 1-way 16A 2 modules with indicator lamp coke grey

CPX161SWL2M_GY

! Discontinued on: 03-Jul-2023

(!) Discontinued

Main

Range	Clipsal
Product Or Component Type	Switch
Device Application	Control
Colour Tint	Coke grey
Type Of Packing	Group

Complementary

Number Of Rocker	1
Device Mounting	Flush
Switch Function	1-way
Control Type	Rocker
Rated Current	16 A at 240 V AC 50 Hz
Local Signalling	Indicator: indicator light, LED (red)
Number Of Modules	2
Material	Plastic
Connections - Terminals	Shrouded terminals
Width	42 mm
Height	48 mm
Depth	37 mm
Resistance To Chemical Agents	Not resistant to alcohols Not resistant to cleaning agent Not resistant to thinner

Environment

Ambient Air Temperature For Operation	-535 °C
Ambient Air Temperature For Storage	-535 °C
Relative Humidity	095 %
Product Certifications	ISI
Standards	IS 3854
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.1 cm
Package 1 Width	5.1 cm
Package 1 Length	4.2 cm
Package 1 Weight	30.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	5.5 cm
Package 2 Width	10.0 cm
Package 2 Length	23.5 cm
Package 2 Weight	361.0 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations