

Product datasheet

Specifications



32A Double Pole Switch, White

E3031DR32_WW

⚠ Discontinued on: 15-Dec-2020

⚠ End-of-service on: 30-Jan-2021

⚠ Discontinued

Main

Range	Neo
Wiring Device Mounting	Surface Flush
Switch Function	2-pole
Switch Application	Switch
Load Type	Resistive Inductive Incandescent lamp
Colour Tint	White

Complementary

Rated Current	32 A at 250 V AC 50/60 Hz
Number Of Gangs	1 gang
Material	Polycarbonate: plastic part
Clamping Connection Capacity	1 x 23 mm ² for solid cable(s) 1 x 23 mm ² for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	16.8 mm
Depth	28.3 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	IEC 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	75 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------