Product datasheet

Specifications





4A Bell Push Switch w/Illuminated "DoNotDisturb&PleaseCleanUp" Sym., Grey Silver

E3031VBPDM_GS

Main

Range	Neo
Product Or Component Type	Control switch
Wiring Device Mounting	Flush Surface
Switch Function	Momentary
Switch Application	Bell
Load Type	Inductive Resistive
Colour Tint	Grey silver

Complementary

Rated Current	4 A at 250 V AC 50/60 Hz
Number Of Gangs	1 gang vertical
Material	Polycarbonate: plastic part
Clamping Connection Capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	23 mm
Depth	36 mm

Environment

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use
Standards	IEC 60669-1 EN 60669-1 GB 16915.1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	68 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	558 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	6580 g

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information