# **Product datasheet**

Specifications





# 4A Bell Push Switch w/Illuminated "DoNotDisturb&PleaseCleanUp" Sym., White

E3031VBPDM\_WW

! Discontinued on: 03-Jul-2023

! Discontinued

#### Main

Range	Neo	
Product Or Component Type	Control switch	
Wiring Device Mounting	Surface Flush	
Switch Function	Momentary	
Switch Application	Bell	
Load Type	pe Inductive Resistive	
Colour Tint	White	

### Complementary

•		
Rated Current	4 A at 250 V AC 50/60 Hz	
Number Of Gangs	1 gang vertical	
Material	Polycarbonate: plastic part	
Clamping Connection Capacity	3 x 2.5 mm² for solid cable(s) 3 x 2.5 mm² for stranded cable(s) 4 x 1.5 mm² for solid cable(s) 4 x 1.5 mm² for stranded cable(s)	
Connections - Terminals	Pillar terminals	
Width	87 mm	
Height	87 mm	
Embedding Depth	23 mm	
Depth	36 mm	

#### **Environment**

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use
Standards	IEC 60669-1 GB 16915.1 EN 60669-1

## **Packing Units**

Unit Type Of Package 1 PCE

Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	68 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	558 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	6580 g

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

<b>②</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information