

# Product datasheet

Specifications



## Electronic Key Card Time Delay Switch, Sliver Bronze

E8431EKT\_SZ

### Main

Range	ZENcelo
Product Or Component Type	Key card switch
Rated Current	16 A at 240 V AC
Colour Tint	Silver bronze

### Complementary

Device Mounting	Surface Flush
Connections - Terminals	Brass terminal
Clamping Connection Capacity	3 x 4 mm <sup>2</sup> for solid cable(s) 3 x 4 mm <sup>2</sup> for stranded cable(s) 2 x 2.5 mm <sup>2</sup> for solid cable(s) 2 x 2.5 mm <sup>2</sup> for stranded cable(s)
Embedding Depth	29.1 mm
Width	87.2 mm
Height	87.2 mm
Depth	41.1 mm

### Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Ambient Air Temperature For Storage	0...60 °C
Standards	GB 16915.2 IEC 60669-2-1

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	184.25 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	60

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	21 cm
Package 2 Width	32.5 cm
Package 2 Length	50 cm
Package 2 Weight	11055 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	480
Package 3 Height	120 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	5316400 g

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

<div>✓</div>	Reach Free Of Svhc	
<div>✓</div>	Toxic Heavy Metal Free	
<div>✓</div>	Mercury Free	
<div>✓</div>	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>