Product datasheet

Specifications





Circuit breaker, FBX, gas insulated switchgear, CCT2 with motor for 990KVA, outdoor and right extensible

FBX3RC0312A21WOC2O

Main

Range Of Product	FBX
Product Or Component Type	Gas insulated switchboard
Device Composition	2 x switch disconnector 630 A 1 x circuit-breaker 630 A
Number Of Functions	3
Enclosure Type	RE (right extensible)
Standards	IEC 62271-1
Network Type	AC
Rated Frequency (Fr)	50 Hz
Rated Voltage (Ur)	12 kV
Rated Continuous Current (Ir)	630 A
Rated Short-Time Withstand Current (Ik)	21 kA rms 3 s

Complementary

Pressure Sensor Type	Standard manometer without contact
Ip Degree Of Protection	Tank with HV parts: IP67 Low voltage control compartment: IP3x Front face + mechanism: IP3x Cable compartment: IP2XC
Bus Rated Current	630 A
Shaft Type	Standard
User Manual	English
Ik Degree Of Protection	IK07
Cable Box Type	Standard without window
Control Type	Manual switch disconnector Motor mechanism 24 V DC O - 3 min - CO circuit breaker
Current Transformer Ratio	30-60/1 A
Local Signalling Voltage Indication	1 fault indication
Interlocking Type	ESW + LBSW
Height	2100 mm
Width	1130 mm
Depth	930 mm
Product Weight	550 kg

Environment

Ambient Air Temperature For Operation	-540 °C
Operating Altitude	<= 1000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	210 cm
Package 1 Width	93 cm
Package 1 Length	113 cm
Package 1 Weight	585 kg

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information