Product datasheet

Specifications





TeSys D - contactor coil - LX4D8 - 24 V DC standard for 115 & 150 A contactor

LX4D8BD

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX4D8
Control Circuit Type	DC standard
[Uc] Control Circuit Voltage	24 V DC
Average Resistance	147 Ohm at 20 °C
Inductance Of Closed Circuit	3.03 H
Product Compatibility	LC1D150 LC1D115
Mechanical Durability	8 Mcycles
Maximum Operating Rate	1200 cyc/h 60 °C

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Operational: 0.751.2 Uc (at <55 °C) Drop-out: 0.150.4 Uc (at <55 °C)
Time Constant	25 ms
Inrush Power In W	270365 W (at 20 °C)
Hold-In Power Consumption In W	2.45.1 W at 20 °C

Environment

Ambient Air Temperature For Operation	-560 °C
Net Weight	0.3 kg

Packing Units

0	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.2 cm
Package 1 Width	11.4 cm
Package 1 Length	17.2 cm
Package 1 Weight	293.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	20

Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.347 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations