

Product datasheet

Specifications

Touch panel 7



MTN6260-1007

⚠ Discontinued on: 01-Nov-2020

⚠ Discontinued

Main

Range Of Product	KNX
Product Or Component Type	Touch panel
Product Destination	KNX bus system
Device Presentation	Device with fixing frame and claws
Bus Type	KNX
Function Available	Touch function
Processor Name	Intel Xscale PXA270 312 MHz

Complementary

Connector Type	RJ45 USB
Device Mounting	Flush
[Ue] Rated Operational Voltage	230 V AC 50 Hz
Maximum Power Consumption In W	4.3 W energy saving mode 8 W operation
Display Type	TFT
Display Resolution	800 x 480 pixels
Display Colour	65000 colours
Display Size	7 inch
Memory Type	64 MB flash 64 MB RAM
Mounting Position	Vertical Horizontal
Material	Plastic
Height	196 mm
Depth	52 mm
Width	137 mm

Environment

Ambient Air Temperature For Operation	-5...45 °C
Ip Degree Of Protection	IP20

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	20.5 cm
Package 1 Length	31 cm
Package 1 Weight	1.32 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)
