Product datasheet

Specification





Spacial CRN tspt door w/o mount.plate. H1000xW600xD300 IP66 IK08 RAL7035..

NSYCRN106300T

! Discontinued on: 01-Nov-2020



Main

Range	Spacial
Product Name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	1000 mm
Enclosure Nominal Width	600 mm
Enclosure Nominal Depth	300 mm
Installation Accessory Type	Wall-mounting
Device Composition	1 body
	1 cable gland plate
	1 door
	1 lock
Door Type	Glazed
Mounting Plate Description	Without mounting plate

Complementary

Body Type	Back welded with double profile forming a protected sealed area Sides made from a single folded section	
Number Of Doors	Front face: 1 door(s)	
Door Opening Side	Reversible (120 °)	
Lock Type	3 mm double-bar lock	
Type Of Gland Plate	Standard	
Accessibility For Operation	Front	
Removable Parts	Door by hinges Cable gland plate by screws	
Material	Body: steel Door: steel and security glass	
Surface Finish	Epoxy-polyester powder	
Colour	Grey (RAL 7035)	
Standards	IEC 62208	
Product Certifications	cUL UL DNV-GL	
Net Weight	25 kg	

Environment

Ip Degree Of Protection	IP66 conforming to IEC 60529	
Ik Degree Of Protection	IK08 conforming to IEC 62262	

Packing Units

r acturing Critico	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	102.0 cm
Package 1 Width	62.0 cm
Package 1 Length	32.0 cm
Package 1 Weight	25.0 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	9
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	196 cm
Package 2 Weight	235 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations