

Product datasheet

Specifications



Fluorescent compact lamp, 11W, 220V, 50/60Hz, socket inglesa - British

NSYLAMCB

⚠ Discontinued on: 01-Nov-2020

⚠ Discontinued

Main

Range Of Product	Lighting and power sockets
Accessory / Separate Part Category	Lighting accessory
Product Or Component Type	Lamp
Device Application	Multi-purpose
Device Composition	fixing elements lamp switch and power socket

Complementary

Outlet Standard	British
Rated Lamp Wattage	11 W
[Ue] Rated Operational Voltage	230 V 50/60 Hz
Bulb Base	2G7
Bulb Type	Fluorescent
Control Type	Built-it switch
Luminous Flux	900 lm
Service Life In Hours	8000 h
Electrical Connection	Screw connector <= 2.5 mm²
Mounting Location	Top front of enclosure
Mounting Support	Cross rails Metal parts DIN rail Upright
Fixing Mode	Screws Clip-in Magnetic fixing
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Thalassa Thalassa PLA Thalassa Thalassa PLM Spacial Spacial SFX Spacial Spacial SMX Spacial Spacial SF Spacial Spacial SM
Material	Light grey plastic
Height	40 mm
Width	372 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	63 mm
-------	-------

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Electrical Insulation Class	Class I
Flame Retardance	V0 conforming to UL 94
Electromagnetic Compatibility	Emission standard for industrial environments conforming to IEC 61000-6-4
Standards	UL 508 A
Product Certifications	VDE
Ambient Air Temperature For Operation	-16...65 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	8.2 cm
Package 1 Length	40 cm
Package 1 Weight	850 g

Contractual warranty

Warranty	18 months
----------	-----------