Product datasheet

Specifications





Wall mounted enclosure, Spacial S3X, stainless steel 304L,double plain door, 1000x1000x300mm, IP55

NSYS3X101030

① Discontinued

Main

Mann	
Range	Spacial
Product Name	Spacial S3X
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	1000 mm
Nominal Width	1000 mm
Nominal Depth	300 mm
Product Installation	Wall-mounting
Device Composition	1 body
	2 door
	1 lock: door
	1 reinforcement frame drilled: door

Complementary

Body Type	Single piece body, cross-shaped structure Gutter shaped front rail
Door Type	Plain
Number Of Doors	Front face: 2 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 3 mm double-bar
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel
Surface Finish	Body and door: Scotch-Brite® brushed Lock: chromium plated
Net Weight	47 kg

Environment

Standards

IEC 62208

Product Certifications	CAN/CSA 22 UL 508 type A
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Environmental Characteristic	Specific hygiene Corrosive

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	101.0 cm
Package 1 Width	101.0 cm
Package 1 Length	31.0 cm
Package 1 Weight	47.0 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	3
Package 2 Height	120 cm
Package 2 Width	125 cm
Package 2 Length	115 cm
Package 2 Weight	156 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations