# **Product datasheet**

Specification





Wall mounted enclosure, Spacial S3X, stainless steel 316L, plain door, 1000x800x300mm, IP66

NSYS3X10830H



#### Main

| Range                     | Spacial   |
|---------------------------|---|
| Product Name              | Spacial S3X   |
| Enclosure Type            | Multi-purpose   |
| Category                  | Compact enclosure   |
| Nominal Height            | 1000 mm   |
| Nominal Width             | 800 mm  |
| Nominal Depth             | 300 mm  |
| Product Installation      | Wall-mounting   |
| <b>Device Composition</b> | 1 body<br>1 reinforcement frame drilled: door<br>1 door<br>2 lock: door |

### Complementary

| Body Type                   | Single piece body, cross-shaped structure Gutter shaped front rail           |
|-----------------------------|--|
| Door Type                   | Plain  |
| Number Of Doors             | Front face: 1 door(s)  |
| Door Opening Side           | Reversible (120 °)   |
| Lock Type                   | 2 points lock, 3 mm double-bar   |
| Mounting Plate Description  | Without mounting plate   |
| Type Of Gland Plate         | Without gland plate  |
| Accessibility For Operation | Front  |
| Removable Parts             | Door by hinges   |
| Material                    | Lock: zamak<br>Hinge: stainless steel<br>Body and door: stainless steel 316L |
| Surface Finish              | Body and door: Scotch-Brite® brushed Lock: chromium plated                   |
| Net Weight                  | 37.6 kg  |

### **Environment**

Standards IEC 62208

| Product Certifications       | CAN/CSA 22<br>UL 508 type A   |
|------------------------------|-------------------------------|
| Ip Degree Of Protection      | IP66 conforming to IEC 60529  |
| Ik Degree Of Protection      | IK10 conforming to IEC 62262  |
| Environmental Characteristic | Specific hygiene<br>Corrosive |

## **Packing Units**

| Unit Type Of Package 1       | PCE      |
|------------------------------|----------|
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 32.0 cm  |
| Package 1 Width              | 82.0 cm  |
| Package 1 Length             | 102.0 cm |
| Package 1 Weight             | 37.6 kg  |
| Unit Type Of Package 2       | PAM      |
| Number Of Units In Package 2 | 6        |
| Package 2 Height             | 176.0 cm |
| Package 2 Width              | 100.0 cm |
| Package 2 Length             | 120.0 cm |
| Package 2 Weight             | 247.0 kg |

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |