Product datasheet

Specifications





ABS box IP66 IK07 RAL7035 Int.H105W105D125 Ext.H116W116D133 Opaque cover H80

NSYTBS111113H

! Discontinued

Main

| Range | Thalassa | |
|---------------------|--|--|
| Product Name | Thalassa TBS | |
| Device Application | Multi-purpose | |
| Category | Industrial box | |
| Height | 116 mm | |
| Width | 116 mm | |
| Depth | 133 mm | |
| Internal Height | 105 mm | |
| Internal Width | 105 mm | |
| Internal Depth | 125 mm | |
| Enclosure Mounting | Wall mounted | |
| Device Composition | 1 body 1 cover 4 cover screw | |
| Quantity Per Set | Set of 2 | |
| Body Type | One piece moulded | |
| Type Of Front Cover | High plain cover | |
| Cover Fixing | Plastic screws | |
| Lock Type | Captive screw flat outside sealed area | |
| Removable Parts | Cover by captive screws | |

Complementary

| Material | ABS (acrylonitrile butadiene-styrene) |
|-------------------------------------|---------------------------------------|
| Colour | Grey (RAL 7035) |
| Standards | IEC 62208 |
| Product Certifications | ΤÜV |
| Electrical Insulation Class | Class II |
| Ip Degree Of Protection | IP66 conforming to NEMA 4.4X |
| Ik Degree Of Protection | IK07 conforming to IEC 62262 |
| Glow Wire Resistance | 650 °C conforming to IEC 60695-2-11 |
| Ambient Air Temperature For Storage | -1540 °C |

| Operating Temperature | -2560 °C | |
|-----------------------|----------|--|
| Net Weight | 0.24 kg | |

Packing Units

| • | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 12 cm |
| Package 1 Width | 12 cm |
| Package 1 Length | 34 cm |
| Package 1 Weight | 240 g |
| Unit Type Of Package 2 | P12 |
| Number Of Units In Package 2 | 360 |
| Package 2 Height | 120 cm |
| Package 2 Width | 80 cm |
| Package 2 Length | 135 cm |
| Package 2 Weight | 107 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ⊘ | Toxic Heavy Metal Free | |
| ⊘ | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |