Product datasheet





ABS box IP66 IK07 RAL7035 Int.H225W175D100 Ext.H241W191D128 Opaque cover H20

NSYTBS241910



Main

Range	Thalassa	
Product Name	Thalassa TBS	
Device Application	Multi-purpose	
Category	Industrial box	
Height	241 mm	
Width	194 mm	
Depth	107 mm	
Internal Height	225 mm	
Internal Width	175 mm	
Internal Depth	100 mm	
Enclosure Mounting	Wall mounted	
Device Composition	1 body 1 cover 4 cover screw	
Body Type	One piece moulded	
Type Of Front Cover	Low plain cover	
Cover Fixing	Plastic screws	
Lock Type	Captive screw flat outside sealed area	
Removable Parts	Cover by captive screws	

Complementary

Material	ABS (acrylonitrile butadiene-styrene)
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	TÜV
Electrical Insulation Class	Class II
Ip Degree Of Protection	IP66 conforming to NEMA 4.4X
Ik Degree Of Protection	IK07 conforming to IEC 62262
Glow Wire Resistance	650 °C conforming to IEC 60695-2-11
Ambient Air Temperature For Storage	-1540 °C
Operating Temperature	-2560 °C

Net Weight 0.7 kg

Packing Units

PCE
1
12 cm
20.5 cm
25.5 cm
687 g
CAR
9
40.5 cm
40 cm
60 cm
7.488 kg
P12
108
120 cm
80 cm
136 cm
95 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations