Product datasheet

Specifications





ABS box IP66 IK07 RAL7035 Int.H225W175D120 Ext.H241W194D127 Opaque cover H40

NSYTBS241912H

(!) Discontinued

Main

Thalassa
Thalassa TBS
Multi-purpose
Industrial box
241 mm
194 mm
127 mm
225 mm
175 mm
120 mm
Wall mounted
1 body 1 cover 4 cover screw
One piece moulded
High plain cover
Plastic screws
Captive screw flat outside sealed area
Cover by captive screws

Complementary

<u> </u>	
Material	ABS (acrylonitrile butadiene-styrene)
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	TÜV
Electrical Insulation Class	Class II
Ip Degree Of Protection	IP66 conforming to NEMA 4.4X
Ik Degree Of Protection	IK07 conforming to IEC 62262
Glow Wire Resistance	650 °C conforming to IEC 60695-2-11
Ambient Air Temperature For Storage	-1540 °C
Operating Temperature	-2560 °C

Net	Weight
-----	--------

Packing Units

r acking onits	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.0 cm
Package 1 Width	20.0 cm
Package 1 Length	25.5 cm
Package 1 Weight	761.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	8
Package 2 Height	40.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	6.852 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	96
Package 3 Height	135.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	92.0 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations