# **Product datasheet**





### ABS box IP66 IK07 RAL7035 Int.H275W225D120 Ext.H291W241D128 Transp.cover H20

NSYTBS292412T

! Discontinued

#### Main

····		
Range	Thalassa	
Product Name	Thalassa TBS	
Device Application	Multi-purpose	
Category	Industrial box	
Height	291 mm	
Nidth 241 mm		
Depth	128 mm	
Internal Height	ernal Height 275 mm	
Internal Width 225 mm		
Internal Depth 120 mm		
Enclosure Mounting	Wall mounted	
Device Composition	1 body 1 cover 4 cover screw	
Body Type	One piece moulded	
Type Of Front Cover	Low transparent cover	
Cover Fixing	king Plastic screws	
Lock Type	Captive screw flat outside sealed area	
Removable Parts	able Parts Cover by captive screws	

### Complementary

Material	ABS (acrylonitrile butadiene-styrene)
Colour	Grey (RAL 7035) Transparent
Standards	IEC 62208
Product Certifications	TÜV
Electrical Insulation Class	Class II
Ip Degree Of Protection	IP66 conforming to NEMA 4.4X
Ik Degree Of Protection	IK07 conforming to IEC 62262
Glow Wire Resistance	650 °C conforming to IEC 60695-2-11
Ambient Air Temperature For Storage	-1540 °C

Operating Temperature	-2560 °C
Net Weight	1.08 kg

# **Packing Units**

PCE
1
12.8 cm
25 cm
31 cm
1.064 kg
CAR
6
60 cm
40 cm
40 cm
7.162 kg
P12
72
120 cm
80 cm
135 cm
96 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations