Product datasheet

Specification





Switch, Livia, 2-way, 10AX, 1 module, IP2X, white

P1002

Main

Range	Livia
Device Application	Control
Product Or Component Type	Switch
Device Presentation	Basic element with central cover plate
Cover Type	Flush cover
Number Of Modules	1
Colour Tint	White (RAL 9003)
Targeted Channel	Do it yourself

Complementary

•	
Device Mounting	Flush
Switch Function	1-pole 2-way
Rated Current	10 AX
[Ue] Rated Operational Voltage	240 V AC
Fixing Mode	Snap-fitted
Material	PC
Local Signalling	without
Warranty	18 months
Net Weight	21.2 g
Embedding Depth	24.1 mm
Switch Application	Control switch
Surface Treatment	Antibacterial
Surface Finish	Glossy
Number Of Terminals	3
Number Of Rocker	1
Height	54.4 mm
Width	22.7 mm
Depth	35.5 mm
Network Frequency	50 Hz
Marking	UP-DOWN
Technology Type	Electromechanical

Connections - Terminals	Screw terminals
Actuator	Rocker

Environment

Ip Degree Of Protection	IP20
Standards	IS 3854

Environmental

Environmental Characteristic	Indoor use
Ambient Air Temperature For Operation	-535 °C
Relative Humidity	1095 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	5.5 cm
Package 1 Length	14.0 cm
Package 1 Weight	24.0 a



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Sustainable Packaging Transparency RoHS/REACh

Resource performance



Sustainable Packaging

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations