Product datasheet

Specifications

Sreen Premium™



"EZinstall3" 2 Key FreeLocate Switch Champagne Gold

U102RWMZB_XCG

() Discontinued on: 03-Jul-2023

(!) Discontinued

Main

Range Of Product	Ulti
Product Or Component Type	RF FreeLocate switch
Operating Distance	100 m
Number Of Channels	2

Complementary

Battery Size	CR2032
Width	87 mm
Height	87 mm
Depth	11.8 mm

Environment

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %

Packing Units

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	12.2 cm
Package 1 Length	12.2 cm
Package 1 Weight	234.4 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	30
Package 2 Height	18 cm
Package 2 Width	31.2 cm
Package 2 Length	56.5 cm
Package 2 Weight	7032 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	300
Package 3 Height	120 cm

Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	2119600 g

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations