

Product datasheet

Specifications



Actassi - modular jack - category 6A - UTP - white - non shuttered

VDIB1775XUWE_E

! Discontinued on: 28 November 2021

VDIB1775XUWE_E has not been replaced. Please contact your customer care centre for more information.

! Discontinued

Main

Range	Actassi
Product brand	Schneider Electric
Product type	30Mech modular jack
Provided equipment	Without shutter
Colour tint	White
Wiring Colour configuration	TIA-568A/B
Type of packing	Plastic bag and carton
Quantity per set	Set of 1

Complementary

[In] rated current	1.5 A at 25 °C
Voltage proof	1000 V AC/DC peak, between contacts
Contact resistance	20 mOhm
Insulation resistance	>= 500 MOhm
Connector type	RJ45
Tool type	Punch down tool Quick termination tool
Cable outer diameter	0.7...1.4 mm
Compatible LAN cable types	UTP
Communication network category	6A
Supported applications	10GBASE-T
Product compatibility	RJ45 plug
Type of footprint	S-110 30 mech
Targeted region	Asia Pacific.

Environment

Operational temperature range	-10...60 °C
Ambient air temperature for storage	-20...70 °C

Climatic category	40/070/21 (21 days)
Flame retardance	UL94-V0 conforming to UL listed
Product certifications	FCC part 68 F IEC 60603-7
Standards	IEC 11801 class E

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	11.0 g
Package 1 Height	0.02 cm
Package 1 width	8.5 cm
Package 1 Length	15 cm
Unit Type of Package 2	S03
Number of Units in Package 2	400
Package 2 Weight	6.82 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	50
Package 3 Weight	750.0 g
Package 3 Height	13 cm
Package 3 width	13 cm
Package 3 Length	18 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
-----------------	-----------