Product datasheet

Specification





Opale switch 2-way 6 A white

X1002WH

Main

Range	Opale
Product Or Component Type	Switch
Device Presentation	Mechanism
Quantity Per Set	Set of 10
Colour Tint	White

Complementary

Technology Type	Electromechanical
Device Mounting	Flush
Number Of Modules	1 module
Actuator	Rocker
Switch Function	2-way
Rated Current	6 A
[Ue] Rated Operational Voltage	240 V
Network Type	AC
Surface Finish	Satin
Network Frequency	50 Hz
Fixing Mode	By captive screws
Connections - Terminals	Shrouded terminals
Material	PC: front cover PA6: base cover
Height	48 mm
Width	21 mm
Depth	35.4 mm

Environment

Standards	IS 3854:1997/A1
Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	-535 °C
Relative Humidity	1095 %
Environmental Characteristic	Indoor use

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	2.1 cm
Package 1 Length	3.3 cm
Package 1 Weight	15 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	5 cm
Package 2 Width	10 cm
Package 2 Length	12 cm
Package 2 Weight	247.2 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	20
Package 3 Height	6.3 cm
Package 3 Width	10.8 cm
Package 3 Length	23.3 cm
Package 3 Weight	305 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations