Product datasheet

Specifications





Opale switch with indicator lamp 1-way 6 A white

X1028WH

Main

Range	Opale
Product Or Component Type	Switch with indicator lamp
Device Presentation	Mechanism
Light Source	Neon
Quantity Per Set	Set of 10
Colour Tint	White

Complementary

Technology Type	Electromechanical	
Device Mounting	Flush	
Number Of Modules	2 modules	
Actuator	Rocker	
Switch Function	1-way	
Rated Current	6 A	
Lamp Function	Indicator	
[Ue] Rated Operational Voltage	240 V	
Network Type	AC	
Surface Finish	Satin	
Network Frequency	50 Hz	
Fixing Mode	By captive screws	
Connections - Terminals	Shrouded terminals	
Material	PC: front cover PA6: base cover	
Height	48 mm	
Width	42 mm	
Depth	35.6 mm	

Environment

Standards	IS 3854:1997/A1
Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	-535 °C
Relative Humidity	1095 %

Environmental Characteristic Indoor use

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.1 cm
Package 1 Width	4.3 cm
Package 1 Length	3.3 cm
Package 1 Weight	17 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	120
Package 2 Height	250 cm
Package 2 Width	265 cm
Package 2 Length	335 cm
Package 2 Weight	2045 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations