Product datasheet

Specifications

 → Green Premium[™]



die-cast empty control station -XAPM - Ø 30.5 - zinc alloy - 4 openings

XAPM4604H29

- () Discontinued on: 20-Oct-2020
- (!) End-of-service on: 21-Nov-2020

Main

Range Of Product	Harmony XAP	
Product Or Component Type	Die-cast empty control station	
Device Short Name	XAPM	
Product Destination	For Ø 30.5 mm control and signalling units	
Product Front Plate Size	80 x 220 mm	
Usable Depth	74.5 mm	
Number Of Cut-Out	4 cut-outs	
Colour Of Base Of Enclosure	Blue	
Colour Of Cover	Blue	
Material	Zinc alloy	
Cable Entry	1 hole without blanking plug for ISO 429248 cable gland, clamping capacity: 25 mm	
Device Mounting	Flush	
Ip Degree Of Protection	IP65 conforming to IEC 60529	

Complementary

Number Of Vertical Rows

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-4070 °C
Overvoltage Category	Class I conforming to IEC 60536 Class I conforming to NF C 20-030

Contractual warranty

Warranty

18 months

1

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations