Product datasheet





LED pilot light with integral lens cap, Harmony XVL, Ø 8, IP40/ IP65, green, covered included, 5 V, faston

XVLA213

(!) Discontinued on: 15-Jun-2023



Main

Range Of Product	Harmony XVL			
Product Or Component Type	onent Type LED pilot light with integral lens cap			
Component Name	XVL			
Mounting Diameter	8 mm			
Light Source	Covered LED			
Light Block Colour	Green			
Protection Type	Built-in by diode Integral ballast resistor			
[Us] Rated Supply Voltage	5 V			
lp Degree Of Protection	IP65 (with seal XVLZ911) conforming to IEC 60529 IP65 (with seal XVLZ911) conforming to NF C 20-010 IP40 conforming to IEC 60529 IP40 conforming to NF C 20-010			

Complementary

Supply Circuit Type	DC	
Connections - Terminals	Tag for Faston connectors: 2.8 x 0.5 mm Tag for soldering connectors	
Current Consumption	25 mA	
[Ui] Rated Insulation Voltage	50 V conforming to IEC 60947-1	
Bulb Lifespan	100000 h	
Nominal Voltage Limit	0.81.1 Un	
Terminals Description Iso N°1	(X1-X2)PL	
Height	10 mm	
Width	10 mm	
Depth	36 mm	
Net Weight	0.003 kg	

Environment

Product Certifications	UL CSA
Protective Treatment	TC
Ambient Air Temperature For Operation	-2570 °C

Ambient Air Temperature For Storage	-4070 °C
Overvoltage Category	Class 3 conforming to IEC 60536 Class 3 conforming to NF C 20-030

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	1.0 cm
Package 1 Length	4.0 cm
Package 1 Weight	3.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	100
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	462.0 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Dimensions Drawings

LED Pilot Light

Dimensions



- (1) Tags for Faston connectors or soldered connections
- e panel thickness: 1 to 8 mm/0.03 to 0.31 in.


С		Ø		
mm	in.	mm in.		
34	1.34	10	0.39	

XVLA213

Mounting and Clearance

LED Pilot Light

Panel Drilling



Ø mi	Ø min G		G min		
mm	in.	mm	in.	mm	in.
8.2	0.32	10.5	0.41	10.5	0.41