



electronic alarm - 16 tones - 0..96 dB - NPN output - black - IP54

XVS96BMBN

Main

Range Of Product	Harmony XVS
Product Or Component Type	Electronic alarm
Device Short Name	XVS

Complementary

Colour	Black
	Didok
Material	PC (polycarbonate): terminal cover
	PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene): body
Marking	CE
Overvoltage Category	Class II conforming to IEC 61140
Mounting Support	96 mm DIN rail
[Us] Rated Supply Voltage	1224 V DC
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
Current Consumption	250 mA at 12 V
	292 mA at 12 V
	292 mA at 24 V
	354 mA at 24 V
Clamping Connection Capacity	<= 1 x 1.5 mm²
Width	96 mm
Height	96 mm
Depth	58.1 mm
Net Weight	0.4 kg

Environment

Discrete Output Type	NPN
Signalling Type	16 tones alarm
Standards	IEC 60947-5-1 IEC 60947-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-3570 °C
Ambient Air Temperature For Operation	-2050 °C
Ip Degree Of Protection	Panel mounted: IP54 conforming to IEC 60529
Noise Level	096 dB (continuous or intermittent tone) at 1 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	14.1 cm
Package 1 Length	14.1 cm
Package 1 Weight	529.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	16
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	9.556 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	320
Package 3 Height	120.0 cm
Package 3 Width	80.0 cm
Package 3 Length	320.0 cm
Package 3 Weight	169.28 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Product datasheet

XVS96BMBN

Dimensions Drawings

Electronic Alarm

Dimensions

