



기본항목

레인지	Prisma
호환성	Prisma G Prisma Pack 250
제품 또는 구성요소 타입	레일
액세서리(부속품 등) / 별도의 부품 카테고리	Installation accessory
레일의 타입	모듈형
설치된 장치	Multi 9: 고정 모듈러 장치 Acti 9: 고정 모듈러 장치 Vigirex: RH10 Vigirex: RH21 Vigirex: RH99 TeSys : fixed GV2LE TeSys : fixed GV2ME TeSys : fixed GV2RTn Multi 9 : fixed modular device <= 40 A Acti 9 : fixed modular device <= 40 A Multi 9 : fixed NG125 with earth leakage protection - control: toggle Multi 9 : fixed NG125 without earth leakage protection - control: toggle Multi 9 : fixed NG125 NA - control: toggle Acti 9 : fixed C120 with earth leakage protection - control: toggle Acti 9 : fixed C120 without earth leakage protection - control: toggle Vigilohm : fixed IM9 Vigilohm : fixed IM9-OL Vigilohm : IM20 Vigilohm : IM20H Compact : fixed INS40 - control: direct front rotary handle - vertical installation Compact : fixed INS63 - control: direct front rotary handle - vertical installation Compact : fixed INS100 - control: direct front rotary handle - vertical installation Compact : fixed INS125 - control: direct front rotary handle - vertical installation Compact : fixed INS160 - control: direct front rotary handle - vertical installation Acti 9 : fixed iC120 with earth leakage protection - control: toggle Acti 9 : fixed iC120 without earth leakage protection - control: toggle Acti 9 : fixed 1/2 or 1 module lamp - horizontal installation Acti 9 : fixed measurement device - horizontal installation Multi 9 : fixed measurement device - horizontal installation
극지 설명	9 x 3P : fixed : GV2LE 9 x 3P : fixed : GV2ME 9 x 3P : fixed : GV2RTn

본 설명서에는 특정 사용자 애플리케이션에 대한 이러한 제품의 적절한 적용 또는 신뢰성을 파악하기 위한 목적용은 대체하는 문서 사용되지 않습니다.

1 x 3P : fixed : NG125  
 1 x 3P : fixed : NG125 NA  
 1 x 3P : fixed : C120  
 1 x 4P : fixed : NG125  
 1 x 4P : fixed : NG125 NA  
 1 x 4P : fixed : C120  
 1 x 3P : fixed : INS40 vertical installation  
 1 x 3P : fixed : INS63 vertical installation  
 1 x 3P : fixed : INS100 vertical installation  
 1 x 3P : fixed : INS125 vertical installation  
 1 x 3P : fixed : INS160 vertical installation  
 1 x 3P : fixed : iC120  
 1 x 4P : fixed : INS40 vertical installation  
 1 x 4P : fixed : INS63 vertical installation  
 1 x 4P : fixed : INS100 vertical installation  
 1 x 4P : fixed : INS125 vertical installation  
 1 x 4P : fixed : INS160 vertical installation  
 1 x 4P : fixed : iC120

## 전기적/기계적 특성

인클로저/구획 칸 설명	플로어 스탠딩 인클로저 - width 600mm 벽 마운트된 인클로저 - width 600mm Pack enclosure - width 600 mm
Number of vertical modules [50 mm]	2 module(s) : 1/2 or 1 module lamp , direct in 600 mm Wide floor-standing enclosure 2 module(s) : 1/2 or 1 module lamp , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : C120 without earth leakage protection , direct in 600 mm Wide floor-standing enclosure 5 module(s) : C120 without earth leakage protection , direct in 600 mm Wide wall-mounted enclosure 3 module(s) : GV2LE , direct in 600 mm Wide floor-standing enclosure 3 module(s) : GV2LE , direct in 600 mm Wide wall-mounted enclosure 3 module(s) : GV2ME , direct in 600 mm Wide floor-standing enclosure 3 module(s) : GV2ME , direct in 600 mm Wide wall-mounted enclosure 3 module(s) : GV2RTn , direct in 600 mm Wide floor-standing enclosure 3 module(s) : GV2RTn , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : iC120 without earth leakage protection , direct in 600 mm Wide floor-standing enclosure 5 module(s) : iC120 without earth leakage protection , direct in 600 mm Wide wall-mounted enclosure 3 module(s) : IM20 in 600 mm Wide floor-standing enclosure 3 module(s) : IM20 in 600 mm Wide wall-mounted enclosure 3 module(s) : IM20H in 600 mm Wide floor-standing enclosure 3 module(s) : IM20H in 600 mm Wide wall-mounted enclosure 3 module(s) : IM9 in 600 mm Wide floor-standing enclosure 3 module(s) : IM9 in 600 mm Wide wall-mounted enclosure 3 module(s) : IM9-OL in 600 mm Wide floor-standing enclosure 3 module(s) : IM9-OL in 600 mm Wide wall-mounted enclosure 4 module(s) : INS100 , direct in 600 mm Wide floor-standing enclosure 4 module(s) : INS100 , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : INS100 , direct in 600 mm Wide floor-standing enclosure 5 module(s) : INS100 , direct in 600 mm Wide wall-mounted enclosure 4 module(s) : INS125 , direct in 600 mm Wide floor-standing enclosure 4 module(s) : INS125 , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : INS125 , direct in 600 mm Wide floor-standing enclosure 5 module(s) : INS125 , direct in 600 mm Wide wall-mounted enclosure 4 module(s) : INS160 , direct in 600 mm Wide floor-standing enclosure 4 module(s) : INS160 , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : INS160 , direct in 600 mm Wide floor-standing enclosure 5 module(s) : INS160 , direct in 600 mm Wide wall-mounted enclosure 4 module(s) : INS40 , direct in 600 mm Wide floor-standing enclosure 4 module(s) : INS40 , direct in 600 mm Wide wall-mounted enclosure 4 module(s) : INS63 , direct in 600 mm Wide floor-standing enclosure 4 module(s) : INS63 , direct in 600 mm Wide wall-mounted enclosure 2 module(s) : measurement device , direct in 600 mm Wide floor-standing enclosure 2 module(s) : measurement device , direct in 600 mm Wide wall-mounted enclosure 2 module(s) : measurement device , direct in 600 mm Wide Pack enclosure 3 module(s) : modular device <= 40 A , direct in 600 mm Wide floor-standing enclosure 3 module(s) : modular device <= 40 A , direct in 600 mm Wide wall-mounted enclosure 8 module(s) : modular device <= 40 A , direct in 600 mm Wide floor-standing enclosure 8 module(s) : modular device <= 40 A , direct in 600 mm Wide wall-mounted enclosure 6 module(s) : modular device <= 40 A , direct in 600 mm Wide Pack enclosure 6 module(s) : modular device , direct in 600 mm Wide Pack enclosure 4 module(s) : modular device , direct in 600 mm Wide floor-standing enclosure 4 module(s) : modular device , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : NG125 without earth leakage protection , direct in 600 mm Wide floor-standing enclosure

5 module(s) : NG125 without earth leakage protection , direct in 600 mm Wide wall-mounted enclosure  
 5 module(s) : NG125 NA , direct in 600 mm Wide floor-standing enclosure  
 5 module(s) : NG125 NA , direct in 600 mm Wide wall-mounted enclosure  
 3 module(s) : RH10 , direct in 600 mm Wide floor-standing enclosure  
 3 module(s) : RH10 , direct in 600 mm Wide wall-mounted enclosure  
 3 module(s) : RH21 , direct in 600 mm Wide floor-standing enclosure  
 3 module(s) : RH21 , direct in 600 mm Wide wall-mounted enclosure  
 3 module(s) : RH99 , direct in 600 mm Wide floor-standing enclosure  
 3 module(s) : RH99 , direct in 600 mm Wide wall-mounted enclosure  
 5 module(s) : C120 with earth leakage protection , direct in 600 mm Wide floor-standing enclosure  
 5 module(s) : C120 with earth leakage protection , direct in 600 mm Wide wall-mounted enclosure  
 5 module(s) : iC120 with earth leakage protection , direct in 600 mm Wide floor-standing enclosure  
 5 module(s) : iC120 with earth leakage protection , direct in 600 mm Wide wall-mounted enclosure  
 5 module(s) : NG125 with earth leakage protection , direct in 600 mm Wide floor-standing enclosure  
 5 module(s) : NG125 with earth leakage protection , direct in 600 mm Wide wall-mounted enclosure

9 mm 피치	48
세트당 수량	1 세트
높이	93.5 mm
너비	600 mm
깊이	50 mm
제품 무게	0.24 kg
색상	회색

### 사용환경

표준	IEC 61439-2 IEC 61439-1
제품 인증	ASEFA

### 상품의 지속 가능성

지속 제공 상태	Green Premium product
RoHS (date code: YYWW)	준수 - since 0807 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
제품 환경 프로필	유효한 <a href="#">유효한</a>
생활 지침의 제품 끝	Need no specific recycling operations

### 계약 보증

보증 기간	18 개월
-------	-------